

		3.0	NP	RP	WP	
		SILVER 3.0	PURPLE 3.5	YELLOW 4.3/5.0	BLUE <b>5.5</b>	<u> </u>
	Final Screw- Unigrip					
	Single Unit 10 Pack DLC Coated* Single Unit	19.068	19.027 19.027-P10 19.227	19.030 19.030-P10 19.230	19.030 19.030-P10 19.230	\$12 \$90 \$20
	Screw head takes Unigrip/S	Star driver				
999	Titanium Analog - For 3D Printed N	<b>1</b> odels				
8 8 8	Single Unit 10 Pack	14.068	14.041 14.041-P10	14.042 14.042-P10	14.069	\$12 \$90
	Use same analog for both 3D prin	iting and sto	ne model			
	Impression Transfer					
	Includes both open & closed tray	screw	17.044	17.045		\$39
	Titanium Healing Abutment	Heights				\$22
		3mm	20.039/3	20.040/3		
		4mm 5mm	20.039/4 20.039/5	20.040/4 20.040/5		
		•	20.000/0	20.0.0,0		
	Straight Titanium Abutment					
S			13.041	13.042		\$49
47	2mm straight polished collar with	17mm chimn	ey with SelectG	rip sandblastea	! surface	
10	Angled Titanium Abutment					
	15°		22.041	22.042		\$75
	25°			23.042		

2mm straight polished collar with 7mm chimney with SelectGrip sandblasted surface

Unless indicated, all abutments include final screw- 3.0 is part # 19.068, NP is part #19.027, and RP/WP is part #19.030. 3.0 platform torque is 15ncm, NP/RP/WP torque is 35ncm.

<sup>\*</sup> DLC Coating is a diamond like coating that reduces friction to deliver a higher gripping force at lower tightening torque value.



		3.0	NP PURPLE 3.5	RP YELLOW 4.3/5.0	W P  BLUE 5.5
Titanium Temporary	Abutment				
	•		24.041	24.042	
	•		25.041	25.042	
All Plastic Castable A	Abutment				
Single Unit			28.041	28.042	
Pack of 10- screw s	old seperately		11.041-P10	11.042-P10	
Single Unit			29.041 12.041-P10	29.042	
Pack of 10- screw so	old seperately		12.041-610	12.042-P10	
Chrome Cobalt Abut	ment				
			30.041	30.042	
Includes wax up	sleeve and find	al screw	31.041	31.042	
Premilled Abutment	Blank				
Titanium	ø10mmD	61.068	61.041	61.042	61.069
Titanium	ø14mmD		62.041	62.042	
Chrome Cobalt	ø14mmD	71.068	71.041	71.042	71.069
Volume discounts a	vailable - Pleas	se contact us for	details		
Desktop Scan Body	- Round top				
			50.041	50.042	
Screw sold seperate	ely use screw #	19.027 (for NF	) and screw# 19	.030 (for RP)	
Titanium Intraoral Sc	can Body				
			52.041	52.042	

 $A \ hard \ anodized \ matted \ surface \ enables \ accurate \ scanning \ . \ Has \ an \ embedded \ screw \ for \ correct \ positioning \ and \ an \ optional \ scan \ body \ driver \ is \ available, \ part \ DTPEI, found \ on \ page \ 8.$ 

Unless indicated, all abutments include final screw- 3.0 is part # 19.068, NP is part #19.027, and RP/WP is part #19.030. 3.0 platform torque is 15ncm, NP/RP/WP torque is 35ncm. Library files for Exocad, 3Shape, and Dental Wings available on website

non-engaging

## **ACTIVE HEX**



### compatible with Nobel Active®, Nobel Replace® Conical Connection, and other Active connection

			<i>3.0</i>	NP	RP	WP	
			SILVER <b>3.0</b>	PURPLE 3.5	YELLOW 4.3/5.0	BLUE <b>5.</b> 5	<u> </u>
3	Scan Body on Ti b	base*	5.0	J. 9	4.0/0.0		\$59
		Non Engagin Engaging	50.500-P10 50.600-P10	50.500-P10 50.600-P10	50.500-P10 50.600-P10	50.500-P10 50.600-P10	
	One size fits all.	Slides over t	ibase and AngleBas	e. No screw req	juired, autoclav	eable and reusabl	e,
	available in pack	eage of 10 onl	y, FREE printable s	scan body STL a	available on wel	site.	
1	Straight TiBase						\$39
		1.2mn	n <mark> </mark>	15.041	15.042		
7 ]		1.5mn	n — 15.068			15.069	
		3.0mn	n <mark> </mark>	15.341	15.342		
1000	Collar Heights	1.2 mi	n 🛑	16.041	16.042		
		1.5mn	16.068			16.069	
		3.0mn	า 🛑	16.341	16.342		
	Plastic sleeves fo	or Straight Ti b	ase **				\$50
		Pack of 5	32.100-P5	32.100-P5	32.100-P5	32.100-P5	
		Pack of 5	33.100-P5	33.100-P5	33.100-P5	33.100-P5	
o d							
_	AngleBase®Ti Bas	e					400
				36.041	36.042		\$39
				37.041	37.042		
	Includes screw pa	art#19.441 (	for NP) and screw p	part# 19.442(fc	or RP)		
	*	*Plastic sleeve	es for casting or pres	ssing. Castable	should be ceme	nted to ti base oni	'y.
_	Plastic sleeves for	AngleBase <sup>®*</sup>					\$50
	Pack o		33.100-P5	33.100-P5	33.100-P5	33.100-P5	
	Pack o	of 5 10°	33.101-P5	33.101-P5	33.101-P5	33.101-P5	

20°

Pack of 5

Unless indicated, all abutments include final screw- 3.0 is part # 19.068, NP is part #19.027, and RP/WP is part #19.030. 3.0 platform torque is 15ncm, NP/RP/WP torque is 35ncm. Library files for Exocad, 3Shape, and Dental Wings available on website

33.102-P5

33.102-P5

33.102-P5

33.102-P5


<sup>\*</sup> The engaging scan body will slide onto the Straight and AngledBase engaging ti bases. The non engaging will slide onto the non engaging. For use in creating restorations using straight ti base and AngleBase. For custom titanium or custom chrome cobalt abutments use desktop or intraoral scan body only.



			4.8		PRICE
			N P	R P	TRICL
	Straight Multiunit Abutment		3.5	4.3/5.0	\$50
		1.5mm 🛑	40.007/1	40.008/1	
	Collar Heights 2.5mm 3.5mm		40.007/2	40.008/2	
			40.007/3	40.008/3	
		4.5mm 🛑		40.008/4	

MULTI-UNIT PLATFORM

Torque is 35ncm. Requires straight multiunit driver, part DTMURP.\*



Angled Multiunit Abu	gled Multiunit Abutment										
17°	2.5mm 🛑	41.707/2	41.708/2		'						
Collar Heights	3.5mm	41.707/3	41.708/3								
30°	3.5mm 🛑	43.007/3	43.008/3								
	4.5mm 🛑	43.007/4	43.008/4								

Includes DLC abutment screw part #19.507 (for NP/3.5) and screw part # 19.508 (for RP /4.3-5.0). Use Unigrip/Star driver.



Impression Transfer for Multiunit\*\* \$39



Includes both open & closed tray screw

#### Closed Tray Impression Transfer for Multiunit\*\*

17.507	\$17
17.507-P4	\$58
17.807	\$17
17.807-P4	\$58
	17.507-P4 17.807

Hand tightens onto multiunit. Available as single and pack of 4 (P4)



Multiunit Titanium Healing Abutment\*\* \$22

20.100

Screws onto multiunit abutment using Unigrip/Star driver screw. Drivers available.

Straight Multiunit Abutment are inserted using straight multiunit driver(part DTMURP- see page #8).

<sup>\*</sup>This is the same straight multiunit driver used on Nobel®, Straumann®, 3i®, BioHorzions® and Megagen® Anyridge multiunits.

<sup>\*\*</sup> Impression transfers and healing abutments can be used on the following multiunits - DESS, Nobel®, 3i®, BioHorzions®, and Megagen® Anyridge.

DLC Coating is a diamond like coating that reduces friction to deliver a higher gripping force at lower tightening torque value.

## **ACTIVE HEX**



## compatible with Nobel Active® Multiunit and DESS Multiunit for Nobel Active®

		MULTI-UNIT PLATFORM 4.8	PRICE
	Desktop Scan Bodyfor Multiunit		\$25
50.007	Screw sold seperately, use screw pa	urt #19.110 50.007	<b>Ş</b> 20
	Intra Oral Scan Body for Multiunit		450
52.007	, ,	52.007 nables accurate scanning . Has an embedded screw for correct ody driver is available, part # DTPEI, found on page 8.	\$50
	Straight Ti Base on top of Multiunit Ab	butments	\$39
I A	4.2mm vertical wall shaft 8.0mm vertical wall shaft	15.007 15.007/8	<b>909</b>
	Includes multiunit screw part #19.		
	Replace with screw part #19.110 f		
	Multiunit Screw (Unigrip) on top of M	Single Unit 19.006	\$12
		Pack of 10 19.006 - P10	\$90
	DLC Coated Torque screws to 15ncm.	- Single Unit 19.006	\$20
	Plastic sleeve for straight ti base on to	p of Multiunit*	\$50
	Pack of 5	32.007-P5	
	AngleBase Ti Base on top of Multiuni		\$39
	Includes AngleBase screw part #19.	36.007 306- requires AngleBase Driver , see Page 8	
	Screw for Multiunit AngleBase	19.306	\$12
	Torque screw to 15ncm.		

DLC Coating is a diamond like coating that reduces friction to deliver a higher gripping force at lower tightening torque value.

non-engaging



#### compatible with Nobel Active® Multiunit and DESS Multiunit for Nobel Active®

		MULTI-UNIT PLATFORM 4.8	<u> </u>
	Multiunit Analog* - For 3D Printed M	odels	
	Single Unit 10 Pack	14.007 14.007-P10	\$12 \$90
	Use same analog for both 3D printing	ng and stone model	
	Titanium Temporary Abutment on top o	f Multiunit	\$39
		24.007	Ų
	All Plastic Castable Abutment on top of	Multiunit	
וביביבי	Single Unit Pack of 10, screw sold seperately	28.007 11.007-P10	\$25 \$90
	Chrome Cobalt Abutment on top of Multi	unit	\$45
		30.007	
	DESS LOC on top of Multiunit		\$65
		88.007	<b>4</b> -5-5

Unless noted, all abutments on top of the multiunit include a unigrip/star driver screw, part #19.006. Torque is 15ncm.

non-engaging

Screws onto the top of the Multiunit\*

<sup>\*</sup>Multiunit Analog can be used for the following multiunits - DESS, Nobel®, 3i®, BioHorzions®, and Megagen® Anyridge.

<sup>\*\*</sup> The DESS LOC will screw onto the top of the following multiunits - DESS, Nobel®, 3i®, BioHorzions®, and Megagen® Anyridge.



				NP PURPLE 3.5	RP YELLOW 4.3/5.0	<u> </u>	<u>C E</u>
	DESS LOC	Gingival F	Height			\$65	
		1.0m	m	88.039/1	88.040/1	•	
		2.0m	m	88.039/2	88.040/2		
1	Torque is 30ncm	3.0m	m	88.039/3	88.040/3		
		4.0m	m	88.039/4	88.040/4		
	DESS LOC Analog						
		Single \	Unit	14.054		\$12	
		Pack of	10	14.054-P10		\$90	
	DESS LOC Transfer						
	Closed tray mad	e 0 <sub>1</sub> 1 01v	1	17.054		\$19	
	DESS LOC Retention	n Kits					
			x1	4.	DLRK-P	\$24	
			x2	divergence up i	o 20° DLRK-P2	2 \$49	
			<b>x</b> 1		חובם ם:		ı
			,, i		DLER-P	\$24	
			x2	divergence up		<b>+</b>	
		div bet		divergence up	to 40°	<b>*</b>	
	Inserts	div bet imį	x2 rergence tween plants		to 40° DLER-P2	\$49	
	Inserts	div bet imp up to 2	x2 rergence tween plants	x4 1.5 lbs / 68	DLER-P2  DLOG DLN2-P	\$49	
	Inserts	div bet imp up to 2 up to 2	x2 rergence tween plants 20°	x4 1.5 lbs / 68 x4 3.0 lbs / 13	DLER-P2  BOG DLN2-Pa  BOG DLN3-Pa	\$49 \$21 4	
	Inserts	div bet imp up to 2 up to 2 up to 2	x2 rergence tween plants 20° 20°	x4 1.5 lbs / 68 x4 3.0 lbs / 13	DLER-P2  BOG DLN2-P4  BOG DLN3-P4  BOG DLN4-P4	\$49 \$21 4 4	
	Inserts	div bet imp  up to 2  up to 2  up to 2  up to 2  up to 2	x2 rergence tween plants 20° 20° 40°	x4 1.5 lbs / 68 x4 3.0 lbs / 13 x4 5.0 lbs / 22	DLER-P2  BOG DLN2-P4  BOG DLN3-P4  BOG DLN1-P4  BOG DLN1-P4	\$21	

Inserts sold in pack of 4



# Drivers, Handles, Adaptors, and Blocks



## compatible with Nobel Active®, Nobel Replace® Conical Connection, and other Active connection

					<u> </u>			
110 1 34	Unigrin/ Star Latch Driver	20mm	24mm	35mm	\$35			
UG L=24	Unigrip/ Star - Latch Driver	DT20U	DT24U	DT35U				
TB06 L=24	AngleBase Latch Driver				\$47			
		DT20TB0	6 DT24TB06	DT35TB06				
	Laboratory handle				\$65			
		MDTLAA						
	Premium laboratory handle	e			\$90			
0.65		PHLAB						
	Thumb Knob Handle				\$45			
	7mı 9mı							
	4x4 Square Driver for inser							
	4X4 oqualo Bilvoi loi illooi	DTMURP	III / IDAIIII O		\$35			
	4x4 Square adaptor for latch style driver							
		TWADAP						
	DESS LOC driver for 4x4 s		h		\$35			
9		DTLOC						
as a second	Adaptor from straumann to		are connection		\$35			
	Later and have deliced and	DTSTSQ	0		\$35			
DIAMOS -	Latch style handpiece ada	ptor for 4x4 Square DTANGSG						
	Manual driver for Intraoral				\$55			
		DTPEI						
DESS	DESS Chrome Cobalt				TBD			
G == 1  Application of the part of the par		CRCO100	00					
	Titanium Placks for Non En	nagging or Angle Co	row Channal Bridge					
	Titanium Blocks for Non En			imm and the length is 20mm				
		63.020 63.040		mm and the length is 40mm	TBD			
					TBD			

TBD - New products coming soon. Visit website for current availability and pricing.



Screws fitting Nobel Active and similar implant system		DESS REFERENCE	EQUIVALENT REF.N° OF ORIGINAL IMPLANT BRAND	PACK OF 10 AVAILABLE	PLATFORM		SCREW	2. HEAD DIAMETER	3. HEAD BASE ANGLE		5. OVERALL LENGTH	6. HEAD LENGTH	7. DISTANCE FROM THREAD TO HEAD	8. THREAD LENGTH	9. THREAD KIND	RECOM- MENDED TORQUE	COMMENTS
	stand	19.027	31168	Pack 10 available	NP	-	UG	2,23	72°	T EATT OK III	7,35	2,20	2,40	2,75	M1,6	35Ncm	Standard screw
		19.227	29282		NP	-	UG	2,23	72°		7,35	2,20	2,40	2,75	M1,6	35Ncm	19.027 DLC coated version
<b>%</b>		19.101		Pack 10 available	NP	-	UG	2,23	O°	0,50	7,35	1,90	2,70	2,75	M1,6	35Ncm	Flat seat screw. Better for bridges, structures and zirconia abutments
9		19.327			NP	*	Torx® 06	2,30	0°		6,95	1,50	2,70	2,75	M1,6	35Ncm	Special screw head design Torx for angulated screw channels up to 25°
	stant	19.030	28815	Pack 10 available	RP	-	UG	2,53	54°		7,35	2,30	2,24	2,81	M2,0	35Ncm	Standard screw
		19.230	36918		RP	-	UG	2,53	54°		7,35	2,30	2,24	2,81	M2,0	35Ncm	19.030 DLC coated version
<u> </u>		19.328			RP	*	Torx® 06	2,60	0°		7,60	1,50	2,10	4,00	M2,0	35Ncm	Special screw head design Torx for angulated screw channels up to 25°
		19.441			NP	*	Torx® 06	2,10	Oo	1,00	7,30	1,40	3,90	2,00	M1,6	35Ncm	Replacement screw for DESS ANGLEBase®
3		19.442			RP	*	Torx® 06	2,45	O°	0,70 PLATFORM	7,20	1,40	3,75	2,05	M2,0	35Ncm	Replacement screw for DESS ANGLEBase®
Screws fitting Multi-unit® im	plant systems																
	standar standar	19.006	29287	Pack 10 available	RP (4,8)		UG	2,00	0°	2,80	3,45	1,35	0,00	2,10	M1,4	15Ncm	Standard screw. Can be used for bridges, structures and Zirconia abutments
		19.206	29285		RP (4,8)		UG	2,00	0°	2,80	3,45	1,35	0,00	2,10	M1,4	15Ncm	19.006 DLC coated version
		19.306			RP (4,8)	*	Torx® 06	2,20	0°		3,60	1,50	0,00	2,00	M1,4	15Ncm	Replacement screw for DESS ANGLEBase® on top of multiunit